



GAR1626TN

by Burndy
Catalog ID: GAR1626TN

Prop 65 Notice

To Rod or Pipe with the Same Connector.

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin plated
U Bolt Type	204
UPC	621945144996
UPC 12 Digit	6219451449966

Dimensions

Dimension - B Length inch	1.88 in
Dimension - Height inch	3.50 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	1.66 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	1 1/4
Conductor - Copper Tube Std Size Range	1 1/4
Conductor - Pipe or Round Tube Size Range	1-1/4 in
Conductor - Rebar Size	11
Conductor - Rebar Size Range	11
Conductor - Rod Size	1.380-1.66 in
Conductor - Rod Size Range	1 1/2-1 5/8

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)