



GAR3909BU

by Burndy
Catalog ID: GAR3909BU

Prop 65 Notice

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG,
12" Pipe, 3/8" Stud, W/ silicon bronze hardware

Product Details

General

Installation Torque Recommended in-lb	200 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	1030
UPC	781810001561
UPC 12 Digit	7818100015611

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	14.00 in
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	12.75 in
Dimension - Width inch	14.75 in
Dimension - Width mm	375 mm

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size	4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Size Range	4-4/0
Conductor - Copper Tube Std Size	12
Conductor - Copper Tube Std Size Range	12
Conductor - Pipe or Round Tube Size	12 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)