

Catamount[®] CABLE FASTENING ACCESSORIES

SPECIFICATIONS:

MATERIAL: NYLON ADHESIVE: SYNTHETIC RUBBER MOUNTING SCREW SIZE: #4







NOTES:

I.APPLICATION TEMPERATURE: 65°F TO 120°F (18°C TO 49°C) STORAGE/SERVICE TEMPERATURE: 32°F TO 158°F (0°C TO 70°C)

2. MECHANICAL STRENGTH: 9 LB / 40 N

- 3.SURFACE PREPARATION: SURFACE SHOULD BE CLEANED WITH ALCOHOL-BASED (IPA) CLEANER BEFORE APPLICATION.
- 4. APPLY WITH PRESSURE AND HOLD FOR 5 SECONDS.
- 5.BONDING TIME: 15 MINUTES MAXIMUM ADHESION: 1 HOUR

6.EXPIRATION DATE INDICATED ON PACKAGING.

CAT. No.	COLOR	A	В	C	D	E	F
MPNY-750-9-*	NATURAL	. 740	. 740	. 152	. 190	. 200	.050
MPNY-750-0-*	BLACK	[18.79]	[18.79]	[3.860]	[4.820]	[5.080]	[1.270]

* DENOTES PACK QTY. "C"= 100, "D"= 500

GENERAL NOTES				Thomas&Betts				
I. ALL DIMENSIONS ARE FOR REFERENCE ONLY. 2. DIMENSIONS IN BRACKETS []	www.tnb.com			A Member of the ABB Group				
ARE IN METRIC UNITS.	DESCRIPTION: 3/4"	x 3/4	CABLE	TIE				
REVISIONS	MOUNTING BASE							
I SEE ERN (2017554)								
FOR APPROVAL SIGNATURES	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:				
& RELEASE DATE. PROJECT NO: 054P000575	054P000575 / (2016272)	10F1	1	WSD -001485				

THIS DRAWING IS INTENDED FOR DESCRIPTIVE PURPOSES ONLY. AND THE RIGHT IS RESERVED TO DEVIATE FROM ANY OF THE DETAILS SHOWN HEREON. COPYRIGHT THOMAS & BETTS CORPORATION. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL.