



CONDUIT TO FLANGE CLIP, 3/4" EMT, 1/2" RIGID, 1/8"–1/4" FLANGE

CATALOG NUMBER

12P24




FEATURES

- Requires only a hammer to install
- Available for EMT, rigid, IMT and aluminum conduit
- Will pivot thru 360°

PRODUCT ATTRIBUTES

Material: Spring Steel
Finish: nVent CADDY Armour
EMT Conduit Size: 3/4"
Rigid Conduit Size: 1/2"
Outer Diameter: 0.866" – 1.181"
Flange Thickness: 1/8" – 1/4"
Ultimate Static Load: 25 lb
Orientation: Top Mount

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER