



Figure similar

30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Metal Operator, Round Non-Illuminated Selector Switch, Short Lever Black with White Insert 2 Position, A-CAM Spring Return from Right UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

| | |
|---|-----------------|
| design of the product | Actuator round |
| Enclosure | |
| number of command points | 1 |
| delivery state as a kit | No |
| Actuator | |
| design of the actuating element | selector switch |
| color of the actuating element | white |
| material of the actuating element | plastic |
| type of unlocking device | without |
| number of switching positions | 2 |
| Front ring | |
| product component front ring | Yes |
| design of the front ring | standard |
| material of the front ring | metal |
| color of the front ring | chrome |
| Holder | |
| material of the holder | Metal |
| General technical data | |
| product component | No |
| • light source | |
| degree of pollution | 1 |
| protection class IP | IP66 |
| operating frequency maximum | 600 1/h |
| Ambient conditions | |
| ambient temperature | |
| • during operation | -35 ... +70 °C |
| • during storage | -40 ... +85 °C |
| Installation/ mounting/ dimensions | |
| shape of the installation opening | round |
| Certificates/ approvals | |
| Further information | |

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SA2ACB>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SA2ACB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SA2ACB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

last modified:

5/31/2021 