

RACK-MOUNT SLIDING SHELF


The Rack-Mount Sliding Shelf allows easy access to shelf-mounted devices. Shelf is 16-gauge steel with 12-gauge steel supports. The entire assembly is finished with RAL 7035 textured light-gray polyester powder paint. The shelf mounts to the front surface of front and back rack angles.

When mounted directly to a frame, load rating is 150 lb. (68 kg) with four rack angle mountings and 75 lb. (34 kg) with front rack angle mounting.

Rack accessories that are shorter than the enclosure depth can be mounted to rack angles or frame accessory brackets attached to grid straps. Order these items separately.

Note: only mount shelves in applications with four points of attachment.

BULLETIN: P20



	D Max	L	J	Shelf Pullout		
Catalog Number	in./mm	in./mm	in./mm	in./mm	Fits Rack Width	Rack Units
P19SHP68	37.40 950	16.72 425	16.20 412	17.00 432	19 in.	2
P19SHP810	41.30 1050	24.59 625	16.20 412	17.00 432	23 in.	2


TOOL-LESS SHELF




An easy-to-install tool-less vented 19-in. shelf. Mounts onto rack angles that have EIA-spaced square holes (.375 in.). Shelf slides open and provides a variable-sized, continuous surface for equipment. Back of shelf has oval cutouts for power and data cables. Accessory hole patterns at back of shelf fit small and large D-rings to help manage cable. Made of steel with a 150 lb. (68 kg) static load rating. Available with RAL 9005 black or RAL 7035 gray polyester powder coat finish.

Note: For square-hole rack angles only!

BULLETIN: DACCY



Minimum and maximum depth measured from rack angle to rack angle





RACK-MOUNT FIXED SHELF

APPLICATION

The PROLINE G2 Rack Mount Frame Shelf mounts to the front and rear rack angles to provide a stationary surface for equipment.

SPECIFICATIONS

- · Mounts to front and rear rack angles
- · Ventilation slots in shelf surface
- 14-guage (1.75mm) steel shelf with 12-gauge (2.5mm) supports
- · Adjustable to fit multi-depth enclosures or rack angle placements
- Mounting hardware included

FINISH


- Polyester powder paint; RAL 7035 textured light gray standard
- · Custom colors available

LOAD RATING

150 lb. (68 kg)

BULLETIN: P40






RACK-ANGLE MOUNTED DRAWER



Steel drawer for 19-in. rack-angle mounting. Mounts to the front surface of the rack angles. Integral steel box contains the drawer and protects surrounding internal equipment. Extends 13 in. (330 mm) on ball bearing slides. Front includes handle and key lock. Finish is RAL 7035 textured light-gray polyester powder paint. Mounting hardware is included.

BULLETIN: P20

Catalog Number	H (mm)	H (in.)	Fits Rack Width	Rack Units
P19DR1US	43	1.69	19 in.	1
P19DR2US	88	3.47	19 in.	2
P19DR3US	132	5.20	19 in.	3



Catalog Number P19WS	Fits Drawe	r
, , ,	Diawe	
	346 mm 13.62	
110		
410 mm 16.14		//</th
		16 GA. STEEL
	DRAWER	87798549

WRITING SURFACE



A 16-gauge steel cover mounts on top of the drawer to serve as a writing surface and drawer cover. Finish is RAL 7035 textured light-gray polyester powder paint.

BULLETIN: P20

nVent.com/HOFFMAN PH 763.422.2211 Spec-01202 F MODULAR ENCLOSURE SOLUTIONS 2



FRAME ACCESSORY BRACKETS



APPLICATION

Frame Accessory Brackets mount directly to the PROLINE G2 frame and are used in place of rack angles to mount rack accessories such as shelves and pull-out shelves.


SPECIFICATIONS

- · Furnished in sets of four
- · 14-gauge (1.75 mm) steel
- · Mounting hardware included

FINISH

Plated

BULLETIN: P40




GUIDES



Equipment Guides help support rack-mounted equipment during installation. Guides mount between two pairs of rack angles. Slotted holes are provided for vertical or lateral adjustment. Furnished in pairs. Guides have plated finish. Mounting hardware included. Rack accessories that are shorter than the enclosure depth can be mounted to rack angles using Adjustable Rack-Mount Rails or Grid Straps. Order these items separately.

BULLETIN: P40

Catalog Number	L mm/in.	Frame Depth mm/in.
P2RG4	225 8.86	400 15.75
P2RG5	325 12.80	500 19.68
P2RG6	425 16.73	600 23.62
P2RG8	625 24.51	800 31.49
P2RG10	825 32.48	1000 39.37






SLIDES



Heavy-duty ball bearing, plated, three-section Slides are 16-in. (406-mm) long and allow 17-in. (423-mm) extension. They are attached to supports that mount between two pairs of rack-mounting angles that have accessory mounting legs. Mounting hardware is furnished. Equipment 16.75-in. (425-mm) wide can be mounted between Slide assemblies installed on 19-in. rack angles. A pair of Slides can support up to 160 lb. (73 kg) at the extended position when load is distributed evenly along the 16-in. (406-mm) Slide length. Requires Rack Angle Adapter Bracket to fit PROLINE. Needs to be used with the Rack Angle Adapter Bracket (PBRAA, PBRAA19 or PBRAA24).

BULLETIN: P20



Catalog Number	Quantity
A16SL2U	2

nVent.com/HOFFMAN PH 763.422.2211 Spec-01202 F MODULAR ENCLOSURE SOLUTIONS 4