

## TYPE 4X AND TYPE 12 FREE-STAND ENCLOSURES ACCESSORY SELECTION GUIDE

(See Accessories for Details)

### PANELS

Catalog Number				Single-Door Single-Access Enclosures										Single-Door Dual-Access Enclosures											
Steel	Conductive	Description	Panel Size	A602418SSFSN4	A722418SSF5N4	A723018SSF5N4	A723618SSF5N4	A902420SSF5N4	A903620SSF5N4	A603624SSF5N4	A722424SSF5N4	A723024SSF5N4	A723624SSF5N4	A903624SSF5N4	A723630SSF5N4	A723636SSF5N4	A903636SSF5N4	A722424SSFSDAN4	A723024SSFSDAN4	A723624SSFSDAN4	A903624SSFSDAN4	A722430SSFSDAN4	A722426SSFSDAN4	A723636SSFSDAN4	A903636SSFSDAN4
A60P24F1	A60P24F1G	Full Panel	48.00 x 20.00 (1219 x 508)	•	• <sup>a</sup>													•							
A60P24F2	A60P24F2G	Half Panel	24.88 x 20.00 (632 x 508)	•	• <sup>a</sup>													•							
A72P24F1	A72P24F1G	Full Panel	60.00 x 20.00 (1524 x 508)			•					•												•	•	•
A72P24F2	A72P24F2G	Half Panel	30.88 x 20.00 (784 x 508)			•					•												•	•	•
A90P24F1	A90P24F1G	Full Panel	78.00 x 20.00 (1981 x 508)					•															•	•	•
A90P24F2	A90P24F2G	Half Panel	39.00 x 20.00 (1013 x 508)	• <sup>a</sup>	• <sup>a</sup>			•			• <sup>a</sup>							•					•	•	•
A72P30F1	A72P30F1G	Full Panel	60.00 x 26.00 (1524 x 660)			•						•													
A72P30F2	A72P30F2G	Half Panel	30.88 x 26.00 (784 x 660)			•						•													
A60P36F1	A60P36F1G	Full Panel	48.00 x 32.00 (1219 x 813)				• <sup>a</sup>		• <sup>a</sup>	•			• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>			• <sup>a</sup>	• <sup>a</sup>			• <sup>a</sup>	
A60P36F2	A60P36F2G	Half Panel	24.88 x 32.00 (632 x 813)				• <sup>a</sup>		• <sup>a</sup>	•			• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>			• <sup>a</sup>	• <sup>a</sup>			• <sup>a</sup>	
A72P36F1	A72P36F1G	Full Panel	60.00 x 32.00 (1524 x 813)			•					•		•	•	•	•	•			•	•			•	
A72P36F2	A72P36F2G	Half Panel	30.88 x 32.00 (784 x 813)			•	• <sup>a</sup>	• <sup>a</sup>	• <sup>a</sup>			•	•	•	•	•	•			•	•			•	
A90P36F1	A90P36F1G	Full Panel	78.00 x 32.00 (1981 x 813)					•				•		•						•				•	
A90P36F2	A90P36F2G	Half Panel	39.88 x 32.00 (1013 x 813)				• <sup>a</sup>		• <sup>a</sup>			•	•	•	•	•	•			•	•			•	

### SWING-OUT PANELS

Catalog Number	Description	Panel Size	A602418SSFSN4	A722418SSF5N4	A723018SSF5N4	A723618SSF5N4	A902420SSF5N4	A903620SSF5N4	A603624SSF5N4	A722424SSF5N4	A723024SSF5N4	A723624SSF5N4	A903624SSF5N4	A723630SSF5N4	A723636SSF5N4	A903636SSF5N4	A722424SSFSDAN4	A723024SSFSDAN4	A723624SSFSDAN4	A903624SSFSDAN4	A722430SSFSDAN4	A722426SSFSDAN4	A723636SSFSDAN4	A903636SSFSDAN4
A72SP24F3	Full Panel	60.00 x 18.81 (1524 x 478)		•							•												•	•
A72SP24F4	Half Panel <sup>c</sup>	30.88 x 18.81 (784 x 478)		•							•												•	•
A72SP30F3	Full Panel	60.00 x 24.81 (1524 x 630)			•						•													
A72SP30F4	Half Panel <sup>c</sup>	30.88 x 24.81 (784 x 630)			•						•													
A72SP36F3	Full Panel	60.00 x 30.81 (1524 x 783)				•					•		•	•	•	•							•	•
A72SP36F4	Half Panel <sup>c</sup>	30.88 x 30.81 (784 x 783)				•					•		•	•	•	•							•	•
A90SP36F3	Full Panel	78.00 x 30.81 (1981 x 783)					•					•		•									•	
A90SP36F4	Half Panel <sup>c</sup>	39.88 x 30.81 (1013 x 783)					•					•		•									•	

### SIDE-MOUNT PANELS

Catalog Number	Steel	Conductive	Description	Panel Size	A602418SSFSN4	A722418SSF5N4	A723018SSF5N4	A723618SSF5N4	A902420SSF5N4	A903620SSF5N4	A603624SSF5N4	A722424SSF5N4	A723024SSF5N4	A723624SSF5N4	A903624SSF5N4	A723630SSF5N4	A723636SSF5N4	A903636SSF5N4	A722424SSFSDAN4	A723024SSFSDAN4	A723624SSFSDAN4	A903624SSFSDAN4	A722430SSFSDAN4	A722426SSFSDAN4	A723636SSFSDAN4	A903636SSFSDAN4	
A60SMP14	A60SMP14G	A60SMP14G	14 Wide Panel (356)	48.00 x 14.00 (1219 x 356)	•						•																
A72SMP14	A72SMP14G	A72SMP14G	14 Wide Panel (356)	60.00 x 14.00 (1524 x 356)		•	•	•			•	•	•	•	•	•	•	•									
A90SMP14	A90SMP14G	A90SMP14G	14 Wide Panel (356)	78.00 x 14.00 (1981 x 356)					•	•																•	
A72SMP20	A72SMP20G	A72SMP20G	20 Wide Panel (508)	60.00 x 20.00 (1524 x 508)							•	•	•	•	•	•	•	•									
A90SMP20	A90SMP20G	A90SMP20G	20 Wide Panel (508)	78.00 x 20.00 (1981 x 508)							•	•	•	•	•	•	•	•									

### HEAVY DUTY PANEL SUPPORTS

Catalog Number	Description	Panel Size	A602418SSFSN4	A722418SSF5N4	A723018SSF5N4	A723618SSF5N4	A902420SSF5N4	A903620SSF5N4	A603624SSF5N4	A722424SSF5N4	A723024SSF5N4	A723624SSF5N4	A903624SSF5N4	A723630SSF5N4	A723636SSF5N4	A903636SSF5N4	A722424SSFSDAN4	A723024SSFSDAN4	A723624SSFSDAN4	A903624SSFSDAN4	A722430SSFSDAN4	A722426SSFSDAN4	A723636SSFSDAN4	A903636SSFSDAN4	
A60FSHDPS	2 Full-Length	57.25 (1454)							• <sup>a</sup>																
A72FSHDPS	Panel	69.25 (1759)		•	•	•			•	•	•	•	•	•	•	•									
A90FSHDPS	Supports	87.25 (2216)					•	•																	•

Millimeter dimensions are in ( ).

- a Requires heavy duty panel supports
- c Fits in top half or bottom half of enclosure

## TYPE 4X AND TYPE 12 FREE-STAND ENCLOSURES ACCESSORY SELECTION GUIDE

(See Accessories for Details)

### PANELS

				Two-Door Single-Access Enclosures											
				A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
Catalog Number	Steel	Conductive	Description	Panel Size											
A60P24F1	A60P24F1	A60P24F1G	Full Panel	48.00 x 20.00 (1219 x 508)	•b	•a,b		•a,b	•a,b						
A60P24F2	A60P24F2	A60P24F2G	Half Panel	24.88 x 20.00 (632 x 508)	•b	•a,b		•a,b	•a,b						
A72P24F1	A72P24F1	A72P24F1G	Full Panel	60.00 x 20.00 (1524 x 508)		•b		•a,b	•b						
A72P24F2	A72P24F2	A72P24F2G	Half Panel	30.88 x 20.00 (784 x 508)	•a,b	•b		•a,b	•b						
A90P24F1	A90P24F1	A90P24F1G	Full Panel	78.00 x 20.00 (1981 x 508)				•b							
A90P24F2	A90P24F2	A90P24F2G	Half Panel	39.00 x 20.00 (1013 x 508)	•a,b	•a,b		•b	•a,b						
A72P30F1	A72P30F1	A72P30F1G	Full Panel	60.00 x 26.00 (1524 x 660)			•b			•b				•b	
A72P30F2	A72P30F2	A72P30F2G	Half Panel	30.88 x 26.00 (784 x 660)			•b			•b				•b	
A60P36F1	A60P36F1	A60P36F1G	Full Panel	48.00 x 32.00 (1219 x 813)				•a,b	•a,b		•a,b	•a,b		•a,b	
A60P36F2	A60P36F2	A60P36F2G	Half Panel	24.88 x 32.00 (632 x 813)				•a,b	•a,b		•a,b	•a,b		•a,b	
A72P36F1	A72P36F1	A72P36F1G	Full Panel	60.00 x 32.00 (1524 x 813)				•b	•a,b		•b	•a,b		•a,b	
A72P36F2	A72P36F2	A72P36F2G	Half Panel	30.88 x 32.00 (784 x 813)				•b	•a,b		•b	•a,b		•a,b	
A90P36F1	A90P36F1	A90P36F1G	Full Panel	78.00 x 32.00 (1981 x 813)					•b			•b		•b	
A90P36F2	A90P36F2	A90P36F2G	Half Panel	39.88 x 32.00 (1013 x 813)				•a,b	•b		•a,b	•b		•b	

### SWING-OUT PANELS

Catalog Number	Description	Panel Size												
A72SP24F3	Full Panel	60.00 x 18.81 (1524 x 478)	•b						•b					
A72SP24F4	Half Panelc	30.88 x 18.81 (784 x 478)	•b						•b					
A72SP30F3	Full Panel	60.00 x 24.81 (1524 x 630)		•b					•b				•b	
A72SP30F4	Half Panelc	30.88 x 24.81 (784 x 630)		•b					•b				•b	
A72SP36F3	Full Panel	60.00 x 30.81 (1524 x 783)			•b					•b				
A72SP36F4	Half Panelc	30.88 x 30.81 (784 x 783)			•b					•b				
A90SP36F3	Full Panel	78.00 x 30.81 (1981 x 783)							•b			•b		•b
A90SP36F4	Half Panelc	39.88 x 30.81 (1013 x 783)							•b			•b		•b

### SIDE-MOUNT PANELS

Catalog Number	Steel	Conductive	Description	Panel Size										
A60SMP14	A60SMP14	A60SMP14G	14 Wide Panel (356)	48.00 x 14.00 (1219 x 356)	•d									
A72SMP14	A72SMP14	A72SMP14G	14 Wide Panel (356)	60.00 x 14.00 (1524 x 356)		•d	•d	•d		•	•	•	•	
A90SMP14	A90SMP14	A90SMP14G	14 Wide Panel (356)	78.00 x 14.00 (1981 x 356)					•	•		•		•
A72SMP20	A72SMP20	A72SMP20G	20 Wide Panel (508)	60.00 x 20.00 (1524 x 508)						•d	•d	•d		•
A90SMP20	A90SMP20	A90SMP20G	20 Wide Panel (508)	78.00 x 20.00 (1981 x 508)								•d		•

### HEAVY DUTY PANEL SUPPORTS

Catalog Number	Description	Panel Size												
A60FSHDPS	2 Full-Length	57.25 (1454)	•b											
A72FSHDPS	Panel	69.25 (1759)	•b	•b	•b			•b	•b	•b			•b	
A90FSHDPS	Supports	87.25 (2216)				•b	•b					•b		•b

Millimeter dimensions are in ( ).

- a Requires heavy duty panel supports
- b Requires center panel supports
- c Fits in top half or bottom half of enclosure
- d Will not fit if other panels are also installed in same enclosure

## TYPE 4X AND TYPE 12 FREE-STAND ENCLOSURES ACCESSORY SELECTION GUIDE

(See Accessories for Details)

### PANELS

Catalog Number				Single-Door Single-Access Enclosures										Single-Door Dual-Access Enclosures											
Steel	Conductive	Description	Panel Size	A602418SSF	A722418SSF	A723018SSF	A723618SSF	A902420SSF	A903620SSF	A603624SSF	A722424SSF	A723024SSF	A723624SSF	A903624SSF	A723630SSF	A903636SSF	A722424SSFSDAN4	A723024SSFSDAN4	A723624SSFSDAN4	A903624SSFSDAN4	A722430SSFSDAN4	A722436SSFSDAN4	A723636SSFSDAN4	A903636SSFSDAN4	
A60P48F1	A60P48F1G	Full Panel	48.00 x 44.00 (1219 x 1118)																						
A72P48F1	A72P48F1G	Full Panel	60.00 x 44.00 (1524 x 1118)																						
A72P48F2	A72P48F2G	Half Panel	30.88 x 44.00 (784 x 1118)																						
A90P48F1	A90P48F1G	Full Panel	78.00 x 44.00 (1981 x 1118)																						
A90P48F2	A90P48F2G	Half Panel	39.88 x 44.00 (1013 x 1118)																						
A72P60F1	A72P60F1G	Full Panel	60.00 x 56.00 (1524 x 1422)																						
A72P60F2	A72P60F2G	Half Panel	30.88 x 56.00 (784 x 1422)																						
A72P72F1	A72P72F1G	Full Panel	60.00 x 68.00 (1524 x 1727)																						
A72P72F2	A72P72F2G	Half Panel	30.88 x 68.00 (784 x 1727)																						
A90P72F1	A90P72F1G	Full Panel	78.00 x 68.00 (1981 x 1727)																						
A90P72F2	A90P72F2G	Half Panel	39.88 x 68.00 (1013 x 1727)																						

### CENTER PANEL SUPPORTS

Catalog Number	Description																								
A60FSCPS	Center Panel Support																								
A72FSCPS	Center Panel Support																								
A90FSCPS	Center Panel Support																								

### CLAMPING NUTS

Catalog Number	Description																								
APS1420CN	1/4-20 Clamping Nut (Qty. 20) for Special Use	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
APS51616CN	1/4-18 Clamping Nut (Qty. 20) for Special Use	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

### CASTERS

Catalog Number	Description	Size																								
DMCKC	Set of 4 Casters	4 high x 3 diameter	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	

### RACK MOUNTING ANGLES L-STYLE (TYPE RP) FOR 19- AND 24-IN. EQUIPMENT

Catalog Number	Description	For Rack Size	No. Units <sup>d</sup>	Angle Length																								
A60RP24F5	2 Full-Length Angles	19 (483)	28	49.00 (1245)	•	•																						
A60RP24F6	2 Half-Length Angles	19 (483)	15	26.25 (677)	•	•																						
A72RP24F5	2 Full-Length Angles	19 (483)	35	61.25 (1556)	•	•																						
A72RP24F6	2 Half-Length Angles	19 (483)	18	31.50 (800)	•	•																						
A90RP24F5	2 Full-Length Angles	19 (483)	45	78.75 (2000)	•	•																						
A90RP24F6	2 Half-Length Angles	19 (483)	23	40.25 (1022)	•	•																						
A72RP30F5	2 Full-Length Angles	24 (610)	35	61.25 (1556)			•																					
A72RP30F6	2 Half-Length Angles	24 (610)	18	31.50 (800)			•																					

Millimeter dimensions are in ( ).

<sup>d</sup> Will not fit if other panels are also installed in same enclosure

## TYPE 4X AND TYPE 12 FREE-STAND ENCLOSURES ACCESSORY SELECTION GUIDE

(See Accessories for Details)

### PANELS

Catalog Number				Two-Door Single-Access Enclosures											
Steel	Conductive	Description	Panel Size	A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD
A60P48F1	A60P48F1G	Full Panel	48.00 x 44.00 (1219 x 1118)	•	• <sup>a</sup>			• <sup>a</sup>	• <sup>a</sup>						
A72P48F1	A72P48F1G	Full Panel	60.00 x 44.00 (1524 x 1118)		•			• <sup>a</sup>	•						
A72P48F2	A72P48F2G	Half Panel	30.88 x 44.00 (784 x 1118)	• <sup>a</sup>	•			• <sup>a</sup>	•						
A90P48F1	A90P48F1G	Full Panel	78.00 x 44.00 (1981 x 1118)					•							
A90P48F2	A90P48F2G	Half Panel	39.88 x 44.00 (1013 x 1118)		• <sup>a</sup>			•		• <sup>a</sup>					
A72P60F1	A72P60F1G	Full Panel	60.00 x 56.00 (1524 x 1422)			•							•		
A72P60F2	A72P60F2G	Half Panel	30.88 x 56.00 (784 x 1422)			•							•		
A72P72F1	A72P72F1G	Full Panel	60.00 x 68.00 (1524 x 1727)				•		• <sup>a</sup>			•	• <sup>a</sup>		• <sup>a</sup>
A72P72F2	A72P72F2G	Half Panel	30.88 x 68.00 (784 x 1727)				•		• <sup>a</sup>			•	• <sup>a</sup>		• <sup>a</sup>
A90P72F1	A90P72F1G	Full Panel	78.00 x 68.00 (1981 x 1727)					•					•		•
A90P72F2	A90P72F2G	Half Panel	39.88 x 68.00 (1013 x 1727)				• <sup>a</sup>		•			• <sup>a</sup>	•		•

### CENTER PANEL SUPPORTS

Catalog Number	Description	A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD
A60FSCPS	Center Panel Support	•											
A72FSCPS	Center Panel Support		•	•	•			•	•	•		•	
A90FSCPS	Center Panel Support					•	•				•	•	

### CLAMPING NUTS

Catalog Number	Description	A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD
APS1420CN	1/4-20 Clamping Nut (Qty. 20) for Special Use	•	•	•	•	•	•	•	•	•	•	•	•
APS51616CN	1/4-18 Clamping Nut (Qty. 20) for Special Use	•	•	•	•	•	•	•	•	•	•	•	•

### CASTERS

Catalog Number	Description	Size	A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD
DMCKC	Set of 4 Casters	4 high x 3 diameter	•	•	•	•	•	•	•	•	•	•	•	•

### RACK MOUNTING ANGLES L-STYLE (TYPE RP) FOR 19- AND 24-IN. EQUIPMENT

Catalog Number	Description	For Rack Size	No. Units <sup>d</sup>	Angle Length	A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD
A60RP24F5	2 Full-Length Angles	19 (483)	28	49.00 (1245)	• <sup>b</sup>	• <sup>b</sup>			• <sup>b</sup>	• <sup>b</sup>						
A60RP24F6	2 Half-Length Angles	19 (483)	15	26.25 (677)	• <sup>b</sup>											
A72RP24F5	2 Full-Length Angles	19 (483)	35	61.25 (1556)		• <sup>b</sup>		• <sup>b</sup>	• <sup>b</sup>							
A72RP24F6	2 Half-Length Angles	19 (483)	18	31.50 (800)		• <sup>b</sup>			• <sup>b</sup>							
A90RP24F5	2 Full-Length Angles	19 (483)	45	78.75 (2000)					• <sup>b</sup>							
A90RP24F6	2 Half-Length Angles	19 (483)	23	40.25 (1022)					• <sup>b</sup>							
A72RP30F5	2 Full-Length Angles	24 (610)	35	61.25 (1556)			• <sup>b</sup>			• <sup>b</sup>				• <sup>b</sup>		
A72RP30F6	2 Half-Length Angles	24 (610)	18	31.50 (800)			• <sup>b</sup>			• <sup>b</sup>				• <sup>b</sup>		

Millimeter dimensions are in ( ).

<sup>a</sup> Requires heavy duty panel supports

<sup>b</sup> Requires center panel supports

<sup>d</sup> Will not fit if other panels are also installed in same enclosure



## TYPE 4X AND TYPE 12 FREE-STAND ENCLOSURES ACCESSORY SELECTION GUIDE

(See Accessories for Details)

### RACK MOUNTING ANGLES U-STYLE (TYPE RA) FOR 19- AND 24-IN. EQUIPMENT

Catalog Number	Description	For Rack Size	No. Units <sup>d</sup>	Angle Length	A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD
A60RA19TH	2 Full-Length Angles	19 (483)	28	49.00 (1245)	• <sup>b</sup>	• <sup>b</sup>			• <sup>b</sup>	• <sup>b</sup>						
A72RA19TH	2 Full-Length Angles	19 (483)	35	61.25 (1556)		• <sup>b</sup>			• <sup>b</sup>	• <sup>b</sup>						
A90RA19TH	2 Full-Length Angles	19 (483)	45	78.75 (2000)					• <sup>b</sup>							
A72RA24TH	2 Full-Length Angles	24 (610)	35	61.25 (1556)							• <sup>b</sup>				• <sup>b</sup>	

Two-Door Single-Access Enclosures																
A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD					

### CLIP NUT PACKAGE

Catalog Number	Description	Size	Fits												
AN1032	Clip Nut (Pkg of 20)	#10-32 Zinc-Plated	RA Type Mnt Angles	•	•	•	•	•	•	•	•	•	•	•	•

### 19-IN. SWING-OUT RACK MOUNTING FRAMES

Catalog Number	Description	For Rack Size	No. Units <sup>d</sup>	Panel Space												
A7230S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)						• <sup>b</sup>						
A7236S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)							• <sup>b</sup>					
A9036S0F19	Full Swing-Out Frame	19 (483)	43	75.36 (1915)								• <sup>b</sup>				• <sup>b</sup>

Millimeter dimensions are in ( ).

<sup>b</sup> Requires center panel support(s) for installation  
<sup>d</sup> 1 unit = 1.75 in. (44 mm)



## TYPE 4X AND TYPE 12 FREE-STAND ENCLOSURES ACCESSORY SELECTION GUIDE

(See Accessories for Details)

### RACK MOUNTING ANGLES U-STYLE (TYPE RA) FOR 19- AND 24-IN. EQUIPMENT

Catalog Number	Description	For Rack Size	No. Units <sup>d</sup>	Angle Length	A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
A60RA19TH	2 Full-Length Angles	19 (483)	28	49.00 (1245)	• <sup>b</sup>	• <sup>b</sup>			• <sup>b</sup>	• <sup>b</sup>						
A72RA19TH	2 Full-Length Angles	19 (483)	35	61.25 (1556)		• <sup>b</sup>			• <sup>b</sup>	• <sup>b</sup>						
A90RA19TH	2 Full-Length Angles	19 (483)	45	78.75 (2000)				• <sup>b</sup>								
A72RA24TH	2 Full-Length Angles	24 (610)	35	61.25 (1556)			• <sup>b</sup>					• <sup>b</sup>			• <sup>b</sup>	

### CLIP NUT PACKAGE

Catalog Number	Description	Size	Fits	A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
AN1032	Clip Nut (Pkg of 20)	#10-32 Zinc-Plated	RA Type Mnt Angles	•	•	•	•	•	•	•	•	•	•	•	•

### 19-IN. SWING-OUT RACK MOUNTING FRAMES

Catalog Number	Description	For Rack Size	No. Units <sup>d</sup>	Panel Space	A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
A7230S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)		• <sup>b</sup>				• <sup>b</sup>				• <sup>b</sup>		
A7236S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)			• <sup>b</sup>				• <sup>b</sup>			• <sup>b</sup>		
A9036S0F19	Full Swing-Out Frame	19 (483)	43	75.36 (1915)				• <sup>b</sup>				• <sup>b</sup>		• <sup>b</sup>		

### WRITING SURFACES

Catalog Number	Description	Fits Drawer	A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
A19WSDR	Hinged Surface	A19DR2U, A19DR4U					• <sup>a</sup>							
DL29WS	Hinged Surface	DL329DR, DL729DR						• <sup>a</sup>					• <sup>a</sup>	

### 19- AND 24-IN. RACK-MOUNTED SHELVES

Catalog Number	Description	For Rack Size	Number of Units <sup>d</sup>	A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
A19SHP6	Pull-Out Shelf	19 (483)	2					• <sup>a</sup>							
DL29SHP	Pull-Out Shelf	24 (610)	2						• <sup>a</sup>					• <sup>a</sup>	
A19SH6	Fixed Shelf	19 (483)	1					• <sup>a</sup>							
DL29SH	Fixed Shelf	24 (610)	1						• <sup>a</sup>					• <sup>a</sup>	

### GUIDES FOR RACK-MOUNTED SHELVES

Catalog Number	Description	Number of Units <sup>d</sup>	A6048185SFSD	A7248185SFSD	A7260185SFSD	A7272185SFSD	A9048205SFSD	A9072205SFSD	A7248245SFSD	A7260245SFSD	A7272245SFSD	A9072245SFSD	A7260365SFSD	A9072365SFSD
AG1U6	Chassis Guides (2)	1					• <sup>a</sup>	• <sup>a</sup>					• <sup>a</sup>	
AG1U8	Chassis Guides (2)	1							• <sup>a</sup>	• <sup>a</sup>			• <sup>a</sup>	

Millimeter dimensions are in ( ).

<sup>a</sup> Requires 2 sets U-style (Type RA) rack mounting angles for installation

<sup>b</sup> Requires center panel support(s) for installation

<sup>d</sup> 1 unit = 1.75 in. (44 mm)





**Notes**