

# DFN

Ventilation fans



**Description:** Two ventilation fan versions: DFN01 for mounting to a surface from below, DFN02 for mounting on top of a surface, with flow always pointing upwards. Extra contact provided for thermostat connection.

**Voltage:** 220-240 VAC.

**Air circulation:** 160 m<sup>3</sup>/h.

**Power of the fan:** 19 Watt.

**Pack quantity:** 1 set with finger guards and mounting screws.

**Note:** For easy connection use wiring kit DFN61.

Description	Item no.
Inside mounting	DFN01
Top mounting	DFN02

*When ventilator holes are not used they can be closed with DFC closing plates.*