



Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs are Circuit Protection Molded Case Circuit Breakers. 1-Pole circuit breaker type BQ. Rated 120V (060A) (AIR 10 kA). Special features: Load side lugs are included.

| | |
|---------------------------------|-------------------------|
| number of poles | 1 |
| suitability for operation | Electrical Distribution |
| Electricity | |
| continuous current rated value | 60 A |
| Model | |
| product brand name | SIEMENS |
| type of electrical connection | BOLT-ON |
| Mechanical Design | |
| depth [in] | 3 in |
| design of the product | BQ |
| height [in] | 4 in |
| width [in] | 1 in |
| General product approval | |
| standard | UL 489 |

last modified:

1/6/2021

