







HOFFMAN

PROLINE G2











2

$4.5 \pm 0.5 \text{ N}\cdot\text{M}$
 $[40 \pm 4.0 \text{ LBF}\cdot\text{IN}]$



3





2X



3



4a



4b



HOFFMAN