








HOFFMAN


PROLINE G2



1  P2AFRB50 (4x) P2AFRB100 (0x) P2AFRB200 (0x)	2  P2AFRB50 (0x) P2AFRB100 (4x) P2AFRB200 (0x)	3  P2AFRB50 (0x) P2AFRB100 (0x) P2AFRB200 (4x)
---	---	---




P2AFRB50



P2AFRB100


$4.5 \pm 0.4 \text{ N}^*\text{M}$
[$40 \pm 4.0 \text{ LBF-IN}$]



2

P2AFRB200

$4.5 \pm 0.4 \text{ N}^*\text{M}$
[$40 \pm 4.0 \text{ LBF-IN}$]



3