

Project Name

Location

Prepared By



## NUVO 65-684

29W LED AREA LIGHT W/PHOTOCELL

### Notes

[www] 12-27-2021 01:40:34

### General

Status	Active
Finish	Bronze
Wattage	29W
Lumen Output	4060L-4640L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

### Specifications

Technology	LED
CRI	70
Voltage	120V-277V
Beam Angle	150x150
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of +50C (+122F)
Dimmable	Yes-Dimmable
Photocell	Yes
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	4.85
Material	Aluminum

### Dimensions

Height (in.)	7.36
Width (in.)	9.13
Extension (in.)	13.62

### Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	PL93XFELHJHY
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

### Additional Information

Additional Information	Type V Lighting Distribution; Dusk to Dawn Lamp
Installation Notes	Suitable for 42-60mm pipe installation
Warranty	5 Year Limited - Fixtures