# **NetKey® Category 6 Punchdown Patch Panels**



### specifications

Category 6/Class E punchdown patch panels shall terminate unshielded twisted 4-pair, 22 - 26 AWG, 100 ohm cable and mount to standard EIA 19 inches or 23 inches racks. Punchdown tool shall properly terminate each conductor for optimum performance. Universal T568A and T568B color-coded wiring schemes included.



#### technical information

Category 6/Class E performance:	Exceeds ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E channel requirements at swept frequencies up to 250 MHz
	Meets ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E component requirements at swept frequencies up to 250 MHz
FCC and ANSI compliance:	Meets ANSI/TIA-1096-A; contacts plated with 50 microinches of gold for superior performance
IEC compliance:	Meets IEC 60603-7 and IEC 60512-99-002
PoE and PoH compliance:	Meets IEEE 802.3af/802.3at and 802.3bt type 3 and type 4. Supports Power over HDBaseT up to 100 watts
c(UL)us Listed:	UL 1863 (Use as communications circuit accessory); CSA standard C22.2
RoHS compliance:	Compliant
Mounting options:	Mounts to standard EIA 19" or 23" racks (23" requires use of extender brackets: PEB1 or PEB2) 12-port suitable for wall mount with WB89D bracket

### key features and benefits

100% performance tested	Confidence that each port delivers specified performance
110 style punchdown termination	Utilizes industry standard termination style and includes wire retention cap
Identification	Write-on areas allow for port and panel identification
Industry standard RJ45 interface	Familiar to end-users; backwards compatible with Category 5e
Angled design (optional)	Facilitates proper bend radius control and minimizes the need for horizontal cable managers

#### applications

Applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet)
- Voice over Internet Protocol (VoIP)



24-port, 1 RU: NKA6PPG24Y 48-port, 2 RU: NKA6PPG48Y

NetKey Category 6 Flat Punchdown Patch Panels

12-port: NK6PPG12WY 24-port, 1 RU: NK6PPG24Y 48-port, 2 RU: NK6PPG48Y

**Termination Tools** 


Punchdown tool: PDT110‡ **CWST** Snipping tool: Stripping tool: **CJAST** 


Replacement retention cap:

DRWCIW-24 **‡Terminates the NetKey Keystone** 

Punchdown Jack Module and NetKey Punchdown Patch Panels.

## **NetKey® Category 6 Punchdown Patch Panels**





Dimensions are in inches. [Dimensions in brackets are metric].

#### **WORLDWIDE SUBSIDIARIES AND SALES OFFICES**

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

