

Project Name

Location

Prepared By



NUVO 65-747

LED SMALL WALL PACK W/PHOTOCEL

Notes

[www] 06-30-2020 02:05:43

General

Status	Active
Fixture Type	Wall Pack
Finish	Black
Wattage	20W
Lumen Output	2608.9L/2920.8L/2703.4L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80+
Voltage	120V-277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Photocell	Has Photocell
Lens Material	Polycarbonate (PC)
Surge Protection	2.5KV
Weight (lb.)	1.98
Material	Cast Aluminum

Dimensions

Height (in.)	8.59
Width (in.)	5.81
Extension (in.)	3.09

Compliance

Safety Listing	cULus - Listed; cULus - Certified
Location Rating	Wet
Energy Star	No
ADA Compliant	Yes
CA T20 / T24 Rationale	California T24 2016 & 2019 JA8 Compliant - Outdoor LED
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------