GFCI RECEPTACLES

MORE SOLUTIONS FOR MORE SAFETY







designed to be better.™

LEGRAND Hydrodyna Communistry Communistry

At Legrand, we've been providing real solutions to real problems for so long, it's almost second nature. From the world's first GFCI receptacle in 1971, to the introduction of ground-breaking SafeLock[™] Protection some 30 years later, we've been delivering GFCI innovations designed to enhance safety, shorten installation times, and increase productivity for more than four decades.


Because of their proven effectiveness, GFCIs are required by code in numerous locations. We've made it our mission to offer intelligently designed solutions for every residential and commercial environment.

Whether the jobs call for receptacles, combination devices, portable, tamper-resistant, weatherresistant, RoHS-compliant, NAFTA-compliant, hospital grade, or specification grade — there's a reliable P&S GFCI innovation for you.









A safety solution for every home.

IT ALL COMES DOWN TO KEEPING PEOPLE SAFE.

That was our goal when we invented the first GFCI receptacle, and it remains our singular focus to this day. Our broad Pass & Seymour product line includes all the residential GFCI devices you'd expect from an industry leader, plus a number of truly innovative solutions designed to meet today's (and tomorrow's) special requirements.



1595TRW

Tamper-Resistant GFCI — helps keep children safe.

- Patented shutter system helps prevent insertion of foreign objects
- Patented SafeLock[™] Protection — if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected
- Meets NEC[®] requirements

RESET	ARLINDIUS 31.	1
	VIB100	

1595SWTTRWCC4

Decorator Switch/GFCI Combination Devices ideal for remodeling.

- User-preferred up-anddown switching combined with standard GFCI safety features
- Provides more function in single-gang opening
- Tamper-Resistant for added safety
- Ideal for bath and kitchen vent fans



RoHS-Compliant GFCI —

designed to meet environmental regulations.

- Meet all the requirements of the Restriction of Hazardous Substances regulations
- Provides the same functionality and protection as our traditional GFCI






1595NTLTRWCC4

Tamper-Resistant Nightlight/ GFCI combination — ensures safety and convenience.

- Sealed nightlight with Lexan[®] lens prevents tampering
- LED illumination with a 20+ year life expectancy means no bulbs to change
- Photocell turns nightlight
 ON in the dark OFF in the daylight

Make nighttime navigation automatic.

Ideal for bathrooms, hallways, kitchens, stairs, nurseries, and more, this award-winning device delivers advanced safety and protection.



OTHER SUGGESTED PRODUCTS



Single-Gang Flush Mount While-In-Use Covers

- Meet NEC[®] requirements for outdoor power
- Corner hinges enable horizontal or vertical installation

Weatherproof While-In-Use Covers

- Corner hinges enable horizontal or vertical installation
- Easy-opening one-finger latch

SPEED AND RELIABILITY ARE THE KEY to successful commercial installations. Our GFCIs are designed to meet those needs ... and then some. That's because we've been offering GFCIs longer than anyone else, so we know what you need to do the job right the first time. Take a look at our innovative line — we'll think you'll find a solution that perfectly matches your needs. Every time.

PT2095NTLTR, PT2095W

P&S PlugTail[™] GFCI the fastest-installing GFCI ever. Period.

- Beats tough deadlines on any commercial job
- Patented plug and connector design enables simultaneous, one-click termination of all terminals
- No exposed terminals creates a finger-safe application before, during, and after installation
- Available in Spec Grade, Hospital Grade, Tamper-Resistant, and LED/Nightlight combinations

Specification Grade GFCI

- 20 amp designed for heavy commercial use
- High-impact-resistant, thermoplastic construction for superior strength and durability
- The most durable GFCI available. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles









Innovations that translate into faster commercial installations.



²⁰⁹⁵TRAW

Audible Alarm GFCI Receptacle

- Audible alert of tripped condition
- Ideal for areas where GFCI indicator light is not readily apparent
- Exceeds UL943 voltage surge requirements
- Withstands 100x the required UL 3kA/6kV voltage surge test cycles





2095HGNTLTRW

Hospital Grade GFCI

- Meets rigorous requirements of Hospital Grade supplement of UL 498
- Available in Tamper-Resistant and LED/Nightlight combinations



2095TRNALA, PT2095HGNALA

NAFTA-Compliant GFCIs designed to meet government regulations.

- GFCIs that meet the requirements of the Buy American provision of the American Recovery and Reinvestment Act
- Provides the same functionality and protection as our traditional GFCI



Residential GFCI Receptacles

Catalog Number	Description	Color	Ratings A. V.		NEMA Config. No.					
TradeMaster®/Spe	TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI									
1595TR*	Decorator	I, W, —, BK, LA, NI, AB, DB	15	125	5-15R					
1595TRS*	with Auto-Ground	I, W, LA	15	125	5-15K					
TradeMaster®/Spec Grade 15 Amp Duplex GFCI										
1595*	Decorator	I, W, —, GRY, BK, RED, LA	15	125	5-15R					
1595S*	with Auto-Ground	I, W, LA	15		5-15K					
TradeMaster® Audible Alarm Tamper-Resistant Duplex GFCI										
1595TRA*	Decorator	I, W, —, BK, LA	15	125	5-15R					
TradeMaster® Isolated Ground Tamper-Resistant Duplex GFCI										
1595IGTR*	Decorator	I, W, —, BK, LA, O	15	125	5-15R					
TradeMaster® Self	-Test Tamper-Resistant Du	olex GFCI								
1596TR*	Decorator	I, W, LA	15	125	5-15R					
Combination Tamp	er-Resistant Single-Pole Sv	vitch/GFCI								
1595SWTTR*CC4	Switch Rating: 15A, 120VAC	I, W, BK, LA	15	125	5-15R					
Combination Tamp	er-Resistant 15 Amp Nightl	ight/GFCI								
1595NTLTR*CC4	Decorator	I, W, BK, LA, NI, AB, DB	15	125	5-15R					
TradeMaster [®] /Spe	c Grade Weather-Resistant	15 Amp Duplex GFCI								
1595TRWR*	Decorator	I, W, —, BK, LA	15	125	5-15R					
RoHS-Compliant T	radeMaster®/Spec Grade Ta	mper-Resistant 15 Amp Duplex 0	FCI							
1595TRR*	Decorator	I, W, LA	15	125	5-15R					

Commercial GFCI Receptacles

			Ratings		NEMA				
Catalog Number	Description	Color	Α.	٧.	Config. No.				
Spec Grade Tamper-Resistant 20 Amp Duplex GFCI									
2095TR*	Decorator	I, W, —, GRY, BK, RED, LA	20	125	5-20R				
2095TRS*	with Auto-Ground	I, W, LA	20	125	J-20K				
Spec Grade 20 Amp Duplex GFCI									
2095*	Decorator	I, W, —, GRY, BK, RED, LA	20	125	E 20D				
20955*	with Auto-Ground	I, W, LA			5-20R				
Hospital Grade Ta	mper-Resistant Duplex GFC	I							
1595HGTR*	15 Amp		15	125	5-15R				
2095HGTR*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R				
Hospital Grade Du	plex GFCI	·							
1595HG*	15 Amp	I, W, GRY, RED, LA	15	125	5-15R				
2095HG*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R				
Spec Grade Isolate	ed Ground Tamper-Resistan	t Duplex GFCI			·				
2095IGTR*	Decorator	I, W, —, GRY, BK, RED, LA, O	20	125	5-20R				
Hospital Grade Iso	lated Ground Tamper-Resis	stant Duplex GFCI			·				
1595IGHGTR*	15 Amp		15	125	5-15R				
2095IGHGTR*	20 Amp	I, W, —, GRY, RED, LA, O	20	125	5-20R				
Combination Tamp	per-Resistant 20 Amp Nighli	ght/GFCI			·				
2095NTLTR*	Decorator	I, W, GRY, LA	20	125	5-20R				
Hospital Grade Co	mbination Tamper-Resistan	t Nightlight/GFCI							
1595HGNTLTR*	15 Amp	I, W, —, RED	15	125	5-15R				
2095HGNTLTR*	20 Amp	I, W, GRY, RED, LA	20	125	5-20R				
Spec Grade Weath	er-Resistant 20 Amp Duples	GFCI							
2095TRWR*	Decorator	I. W. —, GRY, LA	20	125	5-20R				

*Color Designation I lvory W White GRY Gray **BK** Black RED Red LA Light Almond NI Nickel Brown AB Antique Brass **DB** Dark Bronze **0** Orange

Commercial GFCI Receptacles

Catalog Number	Description	Color	Rati A.	ngs V.	NEMA Config. No.				
Spec Grade Audible Alarm Tamper-Resistant 20 Amp Duplex GFCI									
2095TRA*	Decorator	I, W, —, GRY, BK, RED, LA	20	125	5-20R				
Hospital Grade Audible Alarm Tamper-Resistant Duplex GFCI									
1595HGTRA*	15 Amp			125	5-15R				
2095HGTRA*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R				
RoHS-Compliant TradeMaster®/Spec Grade Tamper-Resistant 20 Amp Duplex GFCI									
2095TRR*	Decorator	1	20	125	5-20R				
Spec Grade Self-Te	st 20 Amp Duplex GFCI								
2096*	Decorator	I, W, —, GRY, LA	20	125	5-20R				
Spec Grade Self-Te	st Tamper-Resistant 20 Am	p Duplex GFCI							
2096TR*	Decorator	I, W, LA	20	125	5-20R				
Hospital Grade Self	-Test 20 Amp Duplex GFCI								
2096HG*	Decorator	I, W, —, GRY, RED, LA	20	125	5-20R				
Hospital Grade Self	-Test Tamper-Resistant 20	Amp Duplex GFCI							
2096HGTR*	Decorator	I, W, LA	20	125	5-20R				

Dead Front GFCI Receptacles

			Ratings		NEMA			
Catalog Number	Description	Color	A. V.		Config. No.			
Spec Grade Dead Front GFCI — 1-1/2 HP Motor Control Rating								
2085	20 Amp	I, W, BK, LA	20	125	5-20R			

P&S PlugTail[™] GFCI Receptacles

			Ratings		NEMA			
Catalog Number	Description	Color	Α.	V.	Config. No.			
Spec Grade Duplex	Spec Grade Duplex GFCI							
PT1595*	15 Amp	I, W, GRY, BK, RED, LA	15	125	5-15R			
PT2095*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R			
Spec Grade Tampe	r-Resistant Duplex GFCI							
PT1595TR*	15 Amp	I, W, —, GRY, BK, RED, LA	15	125	5-15R			
PT2095TR*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R			
Hospital Grade Du	plex GFCI							
PT1595HG*	15 Amp		15	125	5-15R			
PT2095HG*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R			
Hospital Grade Tar	nper-Resistant Duplex GFC							
PT1595HGTR*	15 Amp			125	5-15R			
PT2095HGTR*	20 Amp	I, W, GRY, RED, LA	20	125	5-20R			
Spec Grade Tampe	r-Resistant Combination Ni	ghtlight/GFCI						
PT2095NTLTR*	20 Amp	I, W	20	125	5-20R			
Hospital Grade Tar	nper-Resistant Combinatior	Nightlight/GFCI						
PT1595HGNTLTR*	15 Amp	I, W, RED	15	125	5-15R			
PT2095HGNTLTR*	20 Amp	I, W, LA	20	125	5-20R			



Third-Party Compliance:

cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596



		N	NAFTA-Com	pliant GFCI	Receptacles				
*Col Des	or signation		Catalog Number	Description	Color	Rati A.	ngs V.	NEMA Config. No.	
	lvory		NAFTA-Compliant	TradeMaster®/Spec	: Grade Tamper-Resistant Duplex GFCI				
w	White		1595TRNA*	15 Amp		15	125	5-15R	
	Gray		2095TRNA*	20 Amp	––––– I, W, –, GRY, BK, LA	20	125	5-20R	
	Black		NAFTA-Compliant TradeMaster®/Spec Grade Duplex GFCI						
RED	Red		1595NA*	15 Amp		15	125	5-15R	
LA	Light		2095NA*	20 Amp	––––– I, W, –, GRY, BK, LA	20	125	5-20R	
	Almond		NAFTA-Compliant	Hospital Grade Tam	per-Resistant 20 Amp Duplex GFCI				
NI	Nickel		2095HGTRNA*	Decorator	I, W, GRY, RED, LA	20	125	5-20R	
-	Brown		NAFTA-Compliant	Hospital Grade Dup	lex GFCI				
AB	Antique Brass		2095HGNA*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R	
DB	Dark		NAFTA-Compliant Tamper-Resistant Weather-Resistant Duplex GFCI						
	Bronze		1595TRWRNA*	15 Amp	I, W, —, LA,	15	125	5-15R	
			2095TRWRNA*	20 Amp	I, W, —, GRY, LA	20	125	5-20R	

NAFTA-Compliant P&S PlugTail[™] GFCI Receptacles

NAFTA-Compliant Spec Grade Duplex GFCI								
PT1595NA*	15 Amp	I, W, GRY, LA	15	125	5-15R			
PT2095NA*	20 Amp	I, W, —, GRY, BK	20	125	5-20R			
NAFTA-Compliant Spec Grade Tamper-Resistant 20 Amp Duplex GFCI								
PT2095TRNA*	Decorator	I, W, LA	20	125	5-20R			
NAFTA-Compliant I	NAFTA-Compliant Hospital Grade 20 Amp Duplex GFCI							
PT2095HGNA*	Decorator	I, W, GRY, RED	20	125	5-20R			
NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI								
PT2095HGTRNA*	Decorator	I, W, GRY, RED, LA	20	125	5-20R			
NAFTA-Compliant S	Spec Grade Tamper-Resista	ant Combination Nightlight/Duple	ex GFC					
PT1595NTLTRNA*	15 Amp	. I. W	15	125	5-15R			
PT2095NTLTRNA*	20 Amp	1, ••	20	125	5-20R			
NAFTA-Compliant I	Hospital Grade Tamper-Res	istant Combination Nightlight/D	uplex	GFCI				
PT1595HGNTLTRNA*	15 Amp	- I, W		125	5-15R			
PT2095HGNTLTRNA*	20 Amp			125	5-20R			

designed to be better.



Electrical Wiring Systems

P.O. Box 4822 Syracuse, NY 13221-4822 800.776.4035 www.legrand.us/PassandSeymour

570 Applewood Crescent Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca



For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/PassandSeymour. We're eager to put our expertise to work for you.