



Canadian 3-Way Switch, Back and Side-Wire, 15A 347V

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | White |
| UPC Number | 785007196085 | Country Of Origin | Mexico |
| Application Sector | Industrial | Standard | UL 20 |

Technical Information

Contact Rating

15amp, 347vac

Closed Contact Resistance

Toggle

Number of Poles

3-Way

Wattage

3 W

Voltage

347 V
