



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 15A 125V

Features & Benefits

Corrosion-resistant, plated wraparound steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention.

Heavy-duty compact design for easier installation and long lasting performance.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

Side and internal screw-pressure-plateback wire accepts #14 : #10 AWG solid or stranded wire.

All devices fit standard #26 opening wall plate.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007784695	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, cUL CSA

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2
