




adorne Collection
adorne® 15A One-Gang Pop-Out™ Outlet, Magnesium
Part No. ARPTR151GM2



The cleverest way to add power and style, this 15A pop-out wall outlet extends to offer 3-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety

Provides additional power with 3-plug access when extended from wall

Disappears back into the wall with a simple push when not needed

Installs easily in as little as 15 minutes

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	786776178616
Country Of Origin	China	Number of Receptacles	3
Application Sector	Residential	Standard	CULUS

Additional Information

Prop 65 Warning Required No

Technical Information

Phase	Single	Connection	Side and Back Wire
Number of Wires	3	Number of Gangs	1
Number of Poles	Double Pole	Wire Size	#14 - #10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Voltage	125 VAC
Connection Type	Internal Pressure Plates	Environmental Conditions	95 (relative humidity, non-condensing)
