



On-Q
28-inch Enclosure with Hinged Door
Part No. EN2850



This 28-inch enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a hinged door.

Features & Benefits

28-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023135	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023,UL1863), cULus, CSA, RoHS	Type	Enclosure

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Conformant Yes

Product Environmental Profile Yes

Technical Information

Thickness 0.1 in

Enclosure Type

Traditional

Cable Entry (6) rear knockouts, (3) top knockouts, (2) rectangular knockouts for 1-gang electrical box in

Frame

Cold Rolled Steel
