



Industrial Grade Weatherproof Lift Cover For Flanged Inlet/Outlet, 1.96-inch Diameter Opening to Accommodate 15/20A Straight Blade, 15A Turnlok®, 20403 Power Interrupter,

Features & Benefits

Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.

Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.

Covers fit all competitive inlets and outlets.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.

Tamper-proof hinge features permanent, locked-in pins for added security.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007065305
Country Of Origin	Mexico	Construction	Weatherproof
Application Sector	Industrial	Standard	UL listed

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Outlets	1
-------------------	---