



Smooth Metal Wall Plate 1-Gang Duplex 1-Gang Decorator 302/304 Stainless Steel

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Packaged in protective film, with finish-matching screws.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Paintable to match plastic plates.

Specifications

General Info

Product Line	Pass & Seymour	Color	Stainless Steel
UPC Number	785007129755	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	UL 514

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Cutout	Receptacle and Decorator	Thickness	0.032 in
Number of Gangs	2		