



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers). Single pole/3-way versions.

Unique integrated single pole/3-way dimmer with fan speed control. Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007040517	Country Of Origin	China
Application Sector	Residential	Standard	RoHS

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Connection	Back & Side Wired	Contact Rating	120VAC
Number of Poles	3-Way	Wattage	450 W
Speed Range	3-Speed	Voltage	120 V
Environmental Conditions	Indoor Only		