



On-Q
20-inch Enclosure with Hinged Door
Part No. EN2050



This 20-inch enclosure universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts more side lances and side tabs for more flexible mounting. It includes a screw-on cover.

Features & Benefits

20-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023081	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023,UL1863), cULus, CSA, RoHS	Type	Enclosure

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Conformant Yes

Product Environmental Profile Yes

Technical Information

Thickness 0.1 in

Enclosure Type

Traditional

Cable Entry (6) rear knockouts, (3) top knockouts, (2) rectangular knockouts for 1-gang electrical box in

Frame

Cold Rolled Steel
