



On-Q 4-Way Digital Cable Splitter with Coax Network Support

Part No. VM2204V1

This professional-grade digital cable splitter distributes HDTV Antenna/Digital Cable and coax data network signals to three devices. Ideal for MoCA-capable networks.



Features & Benefits

- Mounts in single size module space for Greyfox compatible systems
- 4 LNB inputs, 1 CATV/ANT input, and 4 outputs (combined satellite and CATV/ ANT)
- Compatible with existing and future networks such as MoCA, VoIP, and DOCSIS 3.0
- 6kV Surge Protection on all ports
- Coax networking adapters and splitters are not compatible with satellite television systems

Specifications

General Info

Product Line	On-Q	UPC Number	804428066255
Country Of Origin	China	Application Sector	Residential

Technical Information

Connector	ANSI/SCTE 01 Compliant ECT F-port	Temperature Rating	-40°C to 60°C
Return Loss	INPUT, 5-40MHz: 22dB, 41-550MHz: 25dB, 551-1002MHz: 24dB. OUTPUT, 5-14MHz: 25dB, 15-40MHz: 38dB, 41-200MHz: 30dB, 201-550MHz: 25dB, 551-1002MHz: 24dB dB	Impedance	75 ohms