



Perfect for garages and pantries, this dimmer allows for both manual and automatic motion-activated control. Using motion-sensing technology, it automatically turns lights on when you enter a room, and off when you leave. With manual control, you can even adjust to your preferred light level with the subtle built-in slider. Use on its own to control a light or fixture from a single location, or pair with a second SensaDimmer to control a single light source from two locations. This Motion Sensor Dimmer is meant for single fixtures and small lighting groups that do not exceed 700W. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

For use with incandescent/halogen bulbs, and features manual control (for power and light level), as well as automatic control through motion-sensing technology.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	785007023336	Country Of Origin	China
Number of Switches	1	Standard	cULus

### Technical Information

Connector	Screw Terminals	Number of Gangs	1
Number of Poles	Single Pole, 3-Way	Wattage	700 W
Mounting Type	Box	Sensing Range	180° 600 sq ft
Voltage	120 V	Connection Type	Internal Pressure Plates

---

Sensitivity	Major Motion 35' Minor Motion 20'	Load	Incandescent or LED lamp: 0-600 Watt Fluorescent lamp: 0-600 VA Fan Motor: 1/6 hp
-------------	--------------------------------------	------	---

---

Environmental Conditions	Residential Indoor Use Only
--------------------------	-----------------------------

---