



On-Q  
12VDC 30W Power Supply  
Part No. PW7725

Powers connected home devices by converting high voltage alternating current (AC) to low voltage direct current (DC)



## Features & Benefits

Package includes a DC power supply with 2 ft barrel connector plug and a 1.5 ft AC power plug IEC C13/C14 connections  
Stacks neatly in enclosure with AC1031 power strip

## Specifications

### General Info

Product Line	On-Q	UPC Number	804428028475
Country Of Origin	China	Application Sector	Residential
Standard	UL, cULus, CE, FCC, C-Tick, RoHS		

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Additional Information

RoHS Conformant Yes

### Technical Information

Output Voltage	12 V	Connection	DC Barrel
Input Voltage	100 to 240 (50/60Hz)	Environmental Conditions	10 to 90 (relative humidity, non-condensing)