



## Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 20A 250V



### Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.	One-piece, brass, triple-wipe power contacts for lasting retention.
Heavy-duty compact design for easier installation and long lasting performance.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face.	Terminal compartments isolated from each other for positive conductor containment.
Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.	All devices fit standard #26 opening wall plate.
Tri-drive terminal and mounting screws.	Auto-ground clip assures positive ground.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click <a href="#">here</a> .

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007786446	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 498

#### Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

---

## Technical Information

---

Phase	3	Number of Wires	3
Number of Poles	Double Pole	Wire Size	10-14Awg
Voltage	250 V		

---