



Isolated Ground Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side-Wire 15A 125V

## Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Face color coding by voltage facilitates locating and mating of proper devices.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	UPC Number	785007262629
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Wire Size	#14 - #10	Voltage	125 V

---