

Double pole, Single Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.



## Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007267655
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Voltage	120 V, 600 V
Environmental Conditions	UL94 V2		