



PlugTail® Switch Right Angle Connector 4-Wire, 6-inch Stranded THHN12

Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

For covering patents, see www.legrand.us/patents.

Large crimped and welded brass contacts

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007108507
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498/20		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Contact Rating	120/277Vac	Action	Three pole
----------------	------------	--------	------------

Number of Poles

3-Way

Voltage

120 V
