



A modern upgrade for style and safety, the 20A tamper-resistant designer wall outlets from the adorne Collection install easily for the basic power every home needs, while also elevating a space. All adorne wall outlets are made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

- Replaces any standard outlet with ease, in as little as 10 minutes
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect
- More color options available to fit any style, including finishes to match current hardware and lighting trends
- Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007022704
Country Of Origin	China	Number of Receptacles	2
Application Sector	Residential	Standard	CULUS

### Additional Information

Prop 65 Warning Required	No
--------------------------	----

### Technical Information

Phase	Single	Connection	Side and Back Wire
-------	--------	------------	--------------------

---

Number of Wires	3	Number of Gangs	1
Number of Poles	Double Pole	Wire Size	#14 - #10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Mounting Type	Box	Voltage	125 VAC
Connection Type	Internal Pressure Plates	Environmental Conditions	95 (relative humidity, non-condensing)

---