



Pass and Seymour
LS Series Incandescent Slide Dimmer, Ivory
Part No. LS603PI

Incandescent Slide Dimmer, Preset 3-way, 600W



Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in control

Sleek, sculpted contemporary design. No dirt-catching crevices

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts

Superior heat management

No derating on 600W units

For covering patents, see www.legrand.us/patents

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007158021	Country Of Origin	China
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber

95219

cULus Listed

Yes

Technical Information

Operating Cycles

100000

Number of Poles

Single Pole

Wattage

600 W

Voltage

120 V

Load

600 Watt
