



Pass and Seymour  
Communication Plate, One Gang, 302/304 Stainless Steel  
Part No. SS730



Singlegang, single telephone or cable outlet removable 5/8 ft ID grommet in 7/8-inch fthole. Strap mounted. One #340 yoke. Smooth 302/304 Stainless Steel.

## Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness. Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## Specifications

### General Info

|                   |                |                    |                        |
|-------------------|----------------|--------------------|------------------------|
| Product Line      | Pass & Seymour | UPC Number         | 785007129663           |
| Country Of Origin | United States  | Application Sector | Residential/Commercial |
| Standard          | UL 514         |                    |                        |

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

---

Cutout

Telephone or Cable Outlet

Thickness

0.032 in

---

Number of Gangs

1

---