

Commercial Spec Grade Duplex Receptacle, Side-Wire 20A 250V



## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007585018
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498, WC596		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Wire Size	10-14Awg	Voltage	250 V
-----------	----------	---------	-------

---