



- Smooth Metal Wall Plate, 2-Gang Blank, Strap Mounted, 430 Stainless Steel

## Features & Benefits

Type 430 Stainless Steel, magnetic: .032" nominal thickness.	Brushed finish.
Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and industrial buildings.	Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.	Packaged in protective film, with finish-matching screws.
Variety of special plated finishes.	Paintable to match plastic plates.
Can be silk-screened or engraved, and custom punched with over 300 opening styles.	

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007658248
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL 514		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	143223
cULus Listed	Yes	CSA File Number	17695

### Technical Information

Cutout	Blank	Thickness	0.032 in
Number of Gangs	2		