

## Hospital Grade Quad Receptacle 20A 125V



### Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Shielding walls guard against live-circuit-to-ground shorts.

UL and CSA listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Built-in wire stripping gauge.

Heavy-duty, phosphor bronze contacts.

Split circuit break-off tabs.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007496352	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

#### Technical Information

---

Number of Wires	3	Temperature Rating	Operating Temperature: -40°C to +65°C (-40°F to 150°F) continuous without impact
Number of Poles	Double Pole	Wire Size	#14 - #12
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2 and UL94-5 VA

---