

High-performance splitter designed for digital cable, On Demand, Pay-per-View and high-speed cable Internet.



Features & Benefits

Strong 15 dB RF video amplification improves signal throughout the home system

DC passing between all ports.

Handles up to eight outputs and one input.

Bracket included.

Uses standard F type connectors.

1 GHz Bandwidth.

Specifications

General Info

Product Line	On-Q	UPC Number	804428021629
Country Of Origin	China	Application Sector	Residential
Standard	RoHS		

Additional Information

RoHS Conformant Yes

Technical Information

Number of Ways	8	Connector	Coaxial
Input	1	Temperature Rating	-40 F to 140 F
Insertion Loss	11.1 dB	Return Loss	23.1 dB

Isolation	5-14 MHz: 25dB. 14-40 MHz: 40dB. 40-200 MHz: 35dB. 200-550 MHz: 28dB. 550-750 MHz: 26dB. 750-1000MHz: 24dB.	Impedance	75 ohms
-----------	---	-----------	---------

Output	8
--------	---
