



Pass and Seymour
Isolated Ground TVSS Quad Receptacle, Ivory
Part No. IG420HISP



Isolated Ground Hospital Grade TVSS Quad Receptacle, 20A 125V

Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007125740	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL1449, UL498: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).

Technical Information

Number of Wires	3	Temperature Rating	Operating Temperature: -40°C to +65°C (-40°F to 150°F) continuous without impact
Number of Poles	Double Pole	Wire Size	#14 - #12

Voltage

125 V

Environmental Conditions

Flammability: UL94 V2 and
UL94-5 VA
