



Pass and Seymour
15A, 125V Heavy Duty Spec Grade Plug Load Timer Receptacle, White
Part No. PLT26251W



New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of P&S Plug Load Controllable solutions will take a load off your mind and a load off your customers' electric bills.

Features & Benefits

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007040128	Country Of Origin	China
Application Sector	Commercial	Standard	RoHS, CSA Listed, CulUS, UL Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Phase	Single
Connection	Screw terminals	Number of Wires	3
Temperature Rating	Maximum continuous +60°C, minimum -40° without impact	Number of Poles	Double Pole
Wire Size	#14 -#10 AWG Copper Conductor Only	Voltage	125 V
