



Canadian 1-Pole Lock Switch, Back and Side-Wire, 20A 347V

## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007196399	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 20

### Technical Information

Actuator	Toggle	Contact Rating	20amp, 347vac
----------	--------	----------------	---------------

---

Action	dpdt	Number of Poles	Double Pole
--------	------	-----------------	-------------

---

Voltage	347 V		
---------	-------	--	--

---