



Pass and Seymour  
LS Series Incandescent Slide Dimmer, Light Almond  
Part No. LS600PLA



Incandescent Slide Dimmer, Preset 600W

## Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in. control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007157925
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

---

## Technical Information

---

Operating Cycles	100000	Number of Poles	Single Pole
Wattage	600 W	Voltage	120 V
Load	600 Watt		

---