



**Pass and Seymour**  
**Double Pole, Single Phase AC Manual Motor Controller**  
Part No. 7812PMD



Double Pole, Single Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

## Features & Benefits

High Horsepower rating of 20HP

Constructed of glass-reinforced thermoplastic

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Gull-wing shaped brass terminal pressure clamps

UL508 and cULus Listing of individual device and assembled device within enclosure

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007267662	Country Of Origin	Mexico
Standard	CSA Listed, UL Listed		

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Enclosure Type	NEMA 1

---

Voltage

120 V, 600 V

Environmental Conditions

UL94 V2

---