



Pass and Seymour
Strain Relief Grips
Part No. BOX40



Wide Range, Straight Male, Dust Tight Grip, 1/2-inch, 0.400-0.540.

Features & Benefits

Wide range grips are recommended for use in wiring of enclosures, power boxes, machine tools, and Includes insulated power centers. bushing.

370 lbs breaking strength rating (in US lbs)

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007996166
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Dust Tight		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	NPT Size: 1/2: Cable Dia. Range: 0.400-0.540
Mounting	Consult the Factory for Mounting Recommendations	Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.