



Receptacle 4-Wire 20A 120/208Volt Turnlok®

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007893601
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

Technical Information

Phase	3	Number of Wires	4
Number of Poles	3-Way	Wire Size	0-18Awg
Voltage	120 V		