

## Hospital Grade Quad Receptacle 20A 125V



### Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Shielding walls guard against live-circuit-to-ground shorts.

UL and CSA listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Built-in wire stripping gauge.

Heavy-duty, phosphor bronze contacts.

Split circuit break-off tabs.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007496338	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 498, 1449

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

#### Technical Information

Phase	3	Number of Wires	3
-------	---	-----------------	---

---

Number of Poles

Double Pole

Wire Size

12-14Awg

---

Voltage

125 V

---