



Specification Grade Decorator Switch Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 347V

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007260083	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 20

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17446
------------	-----	-----------------	-------

Technical Information

Actuator	Paddle	Contact Rating	20amp, 347vac
Action	spdt	Number of Poles	Single Pole
Voltage	347 V		
