



Pass and Seymour
Tamper Resistant Display Receptacle 15A 125V with Brass Plate
Part No. 1542TRDR



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly
- Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring
- .032 inch thick brass triple-wipe power contacts for lasting retention
- Auto-ground clip assures positive ground

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007108767
Country Of Origin	United States	Receptacle Type	Straight Blade
Number of Receptacles	1	Construction	Thermoplastic and Brass
Installation Location	On Floor	Type	Floor Box, Tamper-Resistant

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Gangs	1
Number of Gangs	1	Current Rating	15 A

Connector Type	Power	Indoor/Outdoor	Indoor
Cable Entry	No in	NEMA Configuration Code	NEMA 5-15R
Mounting Type	Flush	Number of Outlets	1
Voltage	125 V		
