

Project Name

Location

Prepared By



SATCO S12444

17A21/FR/LED/E26/930/120V

Notes

[www] 06-15-2020 03:20:40

General

Status	Active
Watts	17W
Incandescent Equivalent	125W
Volts	120V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90
Lumens	2000L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	5.20
MOD	2.76

Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes