

Project Name

Location

Prepared By



## SATCO S12446

17A21/FR/LED/E26/950/120V

### Notes

[www] 06-15-2022 03:20:43

### General

Status	Active
Watts	17W
Incandescent Equivalent	125W
Volts	120V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90
Lumens	2000L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	5.20
MOD	2.76

### Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes