

Project Name

Location

Prepared By



## SATCO S12452

21A23/FR/LED/E26/850/120V/ND

### Notes

[www] 06-15-2022 03:20:43

### General

Status	Active
Watts	21W
Incandescent Equivalent	200W
Volts	120V
Shape	A23
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	2900L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	5.60
MOD	2.96

### Additional Information

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	Exempt - >2600 Lumens
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes